

Bayside Gearheads & Siemens Motors

Mounting Kit Selection Chart

Motor Model	Gearhead Configuration	Bayside Part Number	Mounting Kit Part Number	Adapter Length (mm)
1FK603X/1FT603X	In-Line	PS60	MT60-XXX-010	38.8
		PX60	MX60-XXX-010	45.0
		PS90	MT90-XXX-043	35.0
	Right Angle	PX90	MX90-XXX-043	42.0
		RS60	MZ60-XXX-002	47.0
		RS90	MZ90-XXX-043	42.0
		RB90,RD90,RT90	MD90-XXX-XXX	TBD
1FK604X/1FT604X	In-Line	PS90	MT90-XXX-085	48.0
	Right Angle	PX90	MX90-XXX-085	54.0
		RS90	MZ90-XXX-192	47.0
		RB90,RD90,RT90	MD90-XXX-085	24.5
1FK606X/1FT606X	In-Line	PS115	MT115-XXX-010	51.0
	Right Angle	PX115	MX115-XXX-010	60.0
		RS115	MZ115-XXX-010	60.0
		RB115,RD115,RT115	MD115-XXX-010	27.5
1FK608X/1FT608X	In-Line	PS142	MT142-XXX-027	75.0
	Right Angle	RS142	MZ142-XXX-027	74.0
		RB142,RD142,RT142	MD142-XXX-027	40.8
1FK610X/1FT610X	In-Line	PS180	MT180-XXX-096	108.5
	Right Angle	RS180	MZ180-XXX-XXX	TBD
		RB180,RD180,RT180	MD180-XXX-XXX	TBD
1FK613X/1FT613X	In-Line	PS220	MT220-XXX-050	130.0
		PS300	MT300-XXX-XXX	TBD
		RS220	MZ220-XXX-XXX	TBD
	Right Angle	RB220,RD220,RT220	MD220-XXX-001	50.0
		RS300	MZ300-XXX-XXX	TBD
		RB300,RD300,RT300	MD300-XXX-XXX	TBD

Note: Gearhead/motor combinations are based on physical dimensions only. For high torque applications, a larger frame size gearhead might be required. Please contact an Application Engineer for assistance.

Note: To order, specify gearhead part number and mounting kit part number. See catalog for details.

Gearhead Part Number

EXAMPLE: **PS60 - 010 - LB**

PS	Frame	Gearhead	Optional low-backlash
PX	Size	Ratio	
RS			
RB			
RD			
RT			

Mounting Kit Part Number

EXAMPLE: **MT115 - XXX - 039**

MT	Stealth PS	Frame	Gearhead	Mounting
MX	Stealth PX	Size	Ratio	Kit
MZ	Stealth RS			Identifier
MD	Stealth MultiDrive			

Motor Model	Gearhead Configuration	Bayside Part Number	Mounting Kit Part Number	Adapter Length (mm)
1FT503X	In-Line	PS60	MT60-XXX-001	34.3
		PX60	MX60-XXX-001	47.0
	Right Angle	RS60	MZ60-XXX-001	42.0
1FT504X	In-Line	PS90	MT90-XXX-001	36.0
		PX90	MX90-XXX-001	42.0
	Right Angle	RS90	MZ90-XXX-001	42.0
		RB90,RD90,RT90	MD90-XXX-001	24.5
1FT506X	In-Line	PS115	MT115-XXX-039	41.0
		PX115	MX115-XXX-039	43.0
	Right Angle	RS115	MZ115-XXX-039	42.2
		RB115,RD115,RT115	MD115-XXX-039	26.6
1FT507X	In-Line	PS142	MT142-XXX-078	57.0
	Right Angle	RS142	MZ142-XXX-078	64.0
		RB142,RD142,RT142	MD142-XXX-078	36.0
1FT510X	In-Line	PS180	MT180-XXX-010	67.5
	Right Angle	RS180	MZ180-XXX-010	100.0
		RB180,RD180,RT180	MD180-XXX-010	42.5
1FT513X	In-Line	PS220	MT220-XXX-050	130.0
		PS300	MT300-XXX-XXX	TBD
		RS220	MZ220-XXX-XXX	TBD
	Right Angle	RB220,RD220,RT220	MD220-XXX-001	50.0
		RS300	MZ300-XXX-XXX	TBD
		RB300,RD300,RT300	MD300-XXX-XXX	TBD

Sales and Technical Support

Call 1-800-305-4555 for Application Engineering or contact your local Bayside Sales Office:

Cleveland

☎ 216-228-8636
Fax: 216-228-0192

Texas

☎ 512-343-6059
Fax: 512-343-6084

Switzerland

☎ (41) 71-411-9050
Fax: (41) 71-411-9051

Chicago

☎ 847-991-9322
Fax: 847-991-9322

San Jose

☎ 408-719-7492
Fax: 408-719-7488

Singapore

☎ (65) 545-7757
Fax: (65) 545-9959

Rochester

☎ 716-323-9832
Fax: 716-544-1263

London

☎ (44) 1536-267040
Fax: (44) 1536-268866

Osaka

☎ (81) 3-3981-1150
Fax: (81) 3-3981-1180

Boston

☎ 978-827-1381
Fax: 978-827-1392

Frankfurt

☎ (49) 621-595-3260
Fax: (49) 621-595-3266

Seoul

☎ (82) 2-3667-1886
Fax: (82) 2-3667-1887