

Part Number	Description				
Network Accessories					
1	2200011	PCC-10 PC Card Network Adaptor			
2	2200026	LonPoint Type 2 Base plate			
3	2200030	LPR-10 Router module TP/FT-10 toTP/FT-10			
4	2200038	PCLTA-21/FT-10 PCI slot network card			
5	9100029	Monitor steel shelf			
6	9500035	FTNT-2 FTT network terminator			
PC Accessories					
7	2000012	SVGA Monitor 17" 1024x768			
8	2000042	UltraSwitch 100 alike			
9	2000045	UPS Backup 350VA standard			
10	2000047	UPS Backup 600VA			
11	2000069	UPS Backup 1200VA			
12	2000053	Monitor SVGA Touch Screen LCD 15"			
13	2000055	Keyboard, English			
14	2000056	Mouse			
15	2000057	Monitor SVGA Flat Screen LCD 17" VIS			
16	2020005	Modem 56k bauds interne GVC + PCI AZTEC			
17	2020016	Spare New Hard Disk			
18	2020019	Sound-blaster card + vibra			
19	2020020	Video card PCI or ISA			
20	2020030	Ethernet Network card 10/100baseT PCI			
21	2020041	CD-ROM Burner Internal			
22	2090035	Basic PC Windows 98 (Master)			
23	2090036	Basic PC Windows XP (Master)			
24	2090045	KIT KVM 1000' (Slave) PS2 w/adp for USB PC			
25	2510014	Cabinet Workstation for PC & monitor			
26	2510024	Flat screen wall mount bracket			
PC Kit					
27	851ORDI	PC master with Monitor & Echelon Kit			
28	857ORDI	PC kit with RTC w/o monitor			
29	858ORDI	Kit KVM New Slave with monitor			
30	860ORDI	Human Machine Interface			
Software					
31	9291000	Refrigeration Software			
32	9291010	Refrigeration Software Lite			
33	9292000	HVAC Software			
34	9292010	HVAC Software Lite			
35	9293000	Lighting Software			
36	9293010	Lighting Software Lite			
37	9296000	MT-Alliance Software Platform			
39	9296010	MT-Alliance Software Platform Lite version			
38	9296001	Upgrade MT-Alliance software			
40	9298000	EFM Broker List			
41	9298010	Internet Aware License			
Boards					
WITHOUT ENCLOSURE					
42	9500011	MT1 Automatic			
43	9500012	MT1 Automatic for panic button option			

Part Number	Description				
44	9500010	MT0 Central Board			
45	9500018	MT8 Auto			
46	9500590	Temperature Sensor AD590			
47	950336A	Alarm board MT336A w/o enclosure			
48	9503744	Antisweat controller node w/o enclosure			
49	9503810	Repeater w/o enclosure			
50	9503968	Control Module RTC/Scheduler w/o enclosure			
51	9504222	Converter 0-5V/0-10V to PWM			
52	950500Q	MT500 w/o enclosure			
53	950504P	MT504 w/o enclosure			
54	950508P	MT508 w/o enclosure			
55	950512P	MT512 w/o enclosure			
56	950560Q	Communication Gateway piggyback, Ethernet RS232 or RS485			
57	950632F	Controller for Refr. Compr.w/o enclosure			
58	950634B	Ctrlr for 5 refr. circuits w/o enclosure			
59	950636A	EEPR for 5 E-Valve			
60	950636C	DT-EEPR Version 3 dual temp			
61	960635A	One circuit user interface sw-led			

WITH ENCLOSURE

62	9610001	Pull Station for Leak Detect. W/Encl.12X
63	9610010	MT0 Central Board
64	9610011	MT1 Auto
65	9610012	MT1 Auto for panic button w/enclos, sens
66	9610018	MT8 Auto
67	961336A	Alarm board MT336A
68	961336B	Alarm board MT336A with RTC
69	961474A	Valve detector with ABS enclosure and batteries
70	961462C	Case Display rev 4 FTT w/ABS enclosure
71	961500Q	MT500 with enclosure
72	961504P	MT504 with enclosure
73	961508P	MT508 with enclosure
74	961631F	Ctrl for Refr. Compr.+Unld w/bracket
75	961632F	Ctrl for Refr. Compressor w/bracket
76	961634B	Ctrlr for 5 refr. circuits in enclos

ON SNAPTRACK

77	962336A	Alarm board MT336A on snaptrack
78	962336B	Alarm board MT336A on Snaptrack with RTC
79	9623744	Antisweat controller on snaptrack
80	9623810	Repeater on snaptrack
81	9624222	Converter PWM on snaptrack
82	962500Q	MT500 on snaptrack
83	962504P	MT504 on snaptrack
84	962508P	MT508 on snaptrack
85	962512P	MT512 on snaptrack
86	962634B	MT circuit on snaptrack
87	962636A	EEPR Controller for 5 valves
88	962636C	DT-EEPR Version 3 dual temp on snaptrack
89	847REFR	MT-EEPR Combo 10 relay
90	230198	Debonair 71 Non-Programmable Thermostat
91	230199	Debonair 250 7-Day Programmable Thermostat

Anti sweat Kit Control

92	530114	Relay SCR AC 20A-120/240VAC sig:4-32VDC
93	9610101	Panel w/Anti-Sweat 20A 12 relays 30x22"
94	9610102	Panel w/Anti-Sweat 20A 20 relays 40x22"
95	9610103	Panel w/Anti-Sweat 20A 24 relays 42x22"
96	9610104	Panel w/Anti-Sweat 30A 12 relays 36x22"
97	9610105	Panel w/Anti-Sweat 30A 20 relays 46x22"
98	9610106	Panel w/Anti-Sweat 30A 24 relays 50x22"

Prewired Lighting Panels

99	530103	Panel Relay WR 6161 20A/347V Gentec
----	--------	-------------------------------------

Part Number	Description				
100	530104	Panel of 16 relays Gentec HxWxP 19x15x4			
101	530105	Panel of 32 relays Gentec HWP 29.5x20x4			
102	530106	Panel of 48 relays Gentec HWP 49,2x20x4			
103	530107	Panel of 64 relays Gentec HWP 49,2x20x4			
104	9610002	Lighting Ctrl Panel 12 relay 24x20"			
105	9610004	Lighting ctrl panel 4 relay 16x14"			
106	9610008	Lighting ctrl panel 8 relay 24x20"			

Prewired Glycol Panels

107	9610013	3 CKT Glycol control panel 30x24"
-----	---------	-----------------------------------

Solid State Leak detector

108	230012	Leak detector CO analog sig.& dry c.
109	230013	Leak detect Ammoniac analog sig. & dry
110	230014	Leak detector R21/22/141B/142B an/dry
111	230015	Leak detector Diesel analog sig. & dry c
112	230071	Leak detector R23/123/etc...R502 an/dry
113	230145	Leak detector CO2, LCDisplay sig: NO/NC
114	841REFR	Leak Detector Refrigerant Kit R22
115	842REFR	Leak Detector Refrigerant Kit CFC R404/R

Infrared Leak detector

116	845REFR	Multi-Gaz Leak detector Kit 8 zones
117	846REFR	Multi-Gaz Leak detector Kit 16 zones
118	230273	Leak detector IR for R-11 out: analog & dry
119	230274	Leak detector IR for R-12 out: analog & dry
120	230275	Leak detector IR for R-22 out: analog & dry
121	230276	Leak detector IR for R-125 out: analog & dry
122	230277	Leak detector IR for R-134A out: analog & dry
123	230278	Leak detector IR for R-402A / HP80 out: analog & dry
124	230279	Leak detector IR for R-404A out: analog & dry
125	230280	Leak detector IR for R-507 out: analog & dry

Spare Parts

126	2550001	Tubing for air sampling Natural OD=1/4"
127	2550002	Terminaison filter for tube 1/4"
128	2550003	Water trap
129	2550004	Charcoal air filter ass'y for tube 1/4"
130	2550005	Std Accessory Kit 8 zone Monitor
131	2550006	Std Accessory Kit 16 zones Monitor
132	2200037	LonWorks Communication Package gateway
133	2200043	Control Module FTT10 For Multipoint leak Detector

VAV Controlers

134	230287	Prolon VAV Ctrlr Press Dep
135	230288	Prolon VAV Ctrlr PI-L w/Halomo
136	230289	Prolon VAV Ctrlr PI-H w/Halomo
137	230041	Room probe 10k t3 Wall design w/slide control and override

Current Transformer

138	230164	Current Transformer toroidal 600A
139	230165	Current Transformer Toroidal 800A
140	230166	Current Transformer Split Core 600A
141	230167	Current Transformer Split Core 800A
142	230172	Current Transformer Solid Core 1000:5A
143	230173	Current Transformer Split Core 1000:5A
144	230174	Veris Power Transmitter Split Core 400A:4-20mA
145	230175	Veris Power Transmitter Split Core 800A:4-20mA
146	230176	Veris Power Transmitter Split Core 1600A:4-20mA
147	230177	Veris Power Transmitter Split Core 2400A:4-20mA
148	230184	Watt Node Plus 3Y ph to Neu 120V ph to ph 208-240v
149	230185	Watt Node Plus 3D ph to Neu 120-140V ph to ph 208-240v
150	230186	Watt Node Plus 3Y ph to Neu 240V ph to ph 400v

Part Number	Description				
151	230187	Watt Node Plus 3Y ph to Neu 277V ph to ph 480v			
152	230188	Watt Node Plus 3D ph to Neu 277V ph to ph 480v			
153	230189	Watt Node Plus 3Y ph to Neu 347V ph to ph 600v			
154	230190	Split core CT 1200A window = 2"x 2" sig.333V for WattNode			
155	230191	Split core CT 1200A window = 3.5"x 3.5" sig.333V for WattNode			

Temperature & humidity Probes

156	230032	Humidity & temperature sensor in ABS junction box
157	230033	Duct temperature sensor 8" 10K Metal JCT
158	230046	Wall Mount room temperature sensor
159	230048	Averaging sensor
160	230050	ABS Jct Box Outside air sensor
161	230053	Duct temperature sensor 8" ABS Jct Box
162	230059	Product simulator sensor
163	230060	Probe 2252R insertion for hot food 6" plug-in
164	230072	Defrost termination temperature sensor
165	230073	Discharge temperature sensor bullet type
166	230134	Probe, insertion thersistor pig tail
167	230138	Probe, flange mount hot Case
168	230141	Duct humidity sensor 8" ABS Jct Box
169	230159	Box probe, temperature ceiling
170	230178	Humidity 2% & temp. 10K t3 wall sensor
171	230180	Humidity 3% Probe for Refrigerated Case
172	230181	3% Repl Humidity Element For Veris Probe
173	230183	RF Temperature Transmitter
174	230192	Duct temperature probe 8" flange mount
175	230196	Duct temperature probe 12" ABS Jct Box
176	230197	Probe insertion 8" therm 10k Lead SS on teflon 20'

Pressure Probes

177	9520001	Pressure transducer 100psig w/harness
178	9520002	Pressure transducer 500psig w/harness
179	9520004	Pressure transducer 200psig w/harness

Light Level sensor

180	230087	Digital light sensor
181	230142	Light level sensor analog, indoor
182	230143	Light sensor analog, FTT outdoor
183	230154	Light sensor analog, indoor photocell FTT
184	230155	Light sensor analog, outdoor photocell

HVAC Accessories

185	230057	Flow switch
186	230058	PITO tub
187	230074	Emergency blue Pull Station
188	230083	Differential Pressure Transmitter
189	230130	Round Flange
190	230131	Extender for temperature sensor
191	230132	Coupling for temperature sensor
192	530002	D/T Switch toggle SPST 110V
193	9520003	2 speed exhaust plate
194	2510019	Enclosure NEMA 4-12 24x24x6" Inged

Transfomers

195	4000002	Power supply 1A 0-24V PS241F
196	5600012	Transfo 120/240 to 16/32V 100VA close type
197	5600019	Transfo 120 to 24V 500VA close type
198	5600022	Transfo 24V to 24VCT 40VA open screw ter
199	5600025	Transfo 120/240 to 12/24V 100VA closed
200	5600026	Transfo 120/208/240 to 24VCT/32VCT 150VA
201	5600027	Transfo 120/208/240 to 24VCT 20VA
202	5600030	Transfo 120 to 8/16/24V 30VA class 2 open type

Part Number		Description				
203	5600031	Transfo 120 to 16V 75VA class 2 for 4x4"				
204	5600038	Transfo 120/208/240V to 24V 80VA classe 2 Split bobbin				

Sensors Bulk Priced

205	230072	Defrost termination temperature sensor/ BULK / 3000
206	230073	Discharge temperature sensor bullet type / BULK / 3000
207	9520001	Pressure transducer 100psig w/harness / BULK / 250
208	9520002	Pressure transducer 500psig w/harness / BULK / 250
209	9520004	Pressure transducer 200psig w/harness / BULK / 250

RF Accessories

210	230182	RF Receiver RS232
211	9100032	DT-Bracket

Prewired Panel

212	9610027	Alarm node & Repeater panel 16x16x6"
213	9610028	Audio & Visual alarm panel 12x12x4"
214	3900001	Battery 6 volts 1.2Ah

Notes:

Authorized By: