

HOUSING : 360 BRASS

LEADWIRES : 22AWG (7) STRANDED, RIBBON CABLE TINNED
COPPER PVC INSULATED, ORANGE (20 FT)

CERTIFICATION : CSA / UL 300V

RESISTANCE : 10,000 Ω TYPE 2 ± .2°C AT 25°C

DATE	DESCRIPTION	REV.
		08
		07
		06
		05
		04
--	-----	03
--	-----	02
--	-----	01
--	-----	00

SYSTEM :

REFRIGERATION

AUTOMATION / CONTROL :

MICRO THERMO
TECHNOLOGIES
2584 boul. Le Corbusier
Laval, Quebec
Canada, H7S 2K8
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail : mt@microthermo.com

TITLE:

TEMPERATURE SENSOR

PART#: 23-0072

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO :
G.Q.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO :	FILE NAME:
N.T.S	08-30-2004	S-001	PROBE 23-0072