



ECHELON TYPE CABLE 2#16, UNSHIELDED,
19/29 UTP, BELDEN 8471 OR EQUIVALENT.

CABLE 3#18
FROM TRANSFORMER



FACE PLATE

MT-CMP



MT-UNLOADER

SPECIFICATIONS

APPLICATIONS	Control of reciprocating, scroll and screw compressors. Support for up to (2) unloaders per compressor
UNIVERSAL INPUTS (UI)	None
DIGITAL INPUTS (DI)	3 Digital Inputs:(Dry contacts): Low Pressure Switch, Safety Line Switch, Proof of Running Switch
DIGITAL OUTPUT (DO)	2 Form C Relay Outputs: SPDT, 2A, 250Vac. Protected by on–borad breakers
ANALOG OUTPUT (AO)	None
DIMENSIONS	7.44” X 4.0” X 1.5”(w/Unloader) (189mm x 102mm x38mm)
MOUNTING	Panel Mounted Vertically
POWER REQUIREMENT	24Vac Center–tap 1.8VA
ENVIRONMENTAL	Operating and Storage: –40 to 75°C (–40 to 168°F), 5 to 95% RH, non–condensing

**MICRO THERMO**
TECHNOLOGIES

2564 boul. Le Corbusier
Laval, Québec
Canada, H7S 2K6
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail : m@microthermo.com

TITLE:

MT-CMP WITH MT-UNLOADER

PART# 961631F

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO :
G.O.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO :	FILE NAME:
N.T.S	08-24-2004	C-009	MT-CMP-UNLD

		08
		07
		06
		05
		04
		03
		02
		01
		00
DATE	DESCRIPTION	REV.

SYSTEM :

REFRIGERATION

AUTOMATION / CONTROL :

**MICRO THERMO**
TECHNOLOGIES

2564 boul. Le Corbusier
Laval, Québec
Canada, H7S 2K6
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail : m@microthermo.com