



ECHELON TYPE CABLE 2#16, UNSHIELDED,
19/29 UTP, BELDEN 8471 OR EQUIVALENT.



SPECIFICATIONS

APPLICATIONS	Control of up to (5) refrigeration EEPR valves Sporlan (CDS-9, CDS-16, CDS-17), Alco (ESR 12, ESR24)
UNIVERSIAL INPUTS (UI)	None
DIGITAL INPUTS (DI)	None
DIGITAL OUTPUT (DO)	None
ANALOG OUTPUT (AO)	None
OUTPUT	Stepper Motor Output 400mA
MANUAL CONFIGURATION	MAN/AUTO, OPEN, CLOSE, INIT, SET
DIMENSIONS	8.0" X 4.0" X 1.25" (204mm x 102mm x32mm)
MOUNTING	Plastic SnapTrak or SB Metal Enclosure
POWER REQUIREMENT	24Vac 10.2VA
ENVIRONMENTAL	Operating and Storage: -40 to 75°C (-40 to 168°F), 5 to 95% RH, non-condensing



	08
	07
	06
	05
	04
--	03
--	02
--	01
--	00
DATE	DESCRIPTION
REV.	

SYSTEM :

REFRIGERATION

AUTOMATION / CONTROL :

**MICRO THERMO**
T E C H N O L O G I E S

2584 boul. Le Corbusier
Laval, Quebec
Canada, H7S 2K8
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail : mt@microthermo.com

TITLE:
MT-EEPR

PART# 962636A

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO :
G.Q.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO :	FILE NAME:
N.T.S	08-24-2004	C-007	MT-EEPR-CON