




SPECIFICATIONS

APPLICATIONS	Control of up to (5) refrigeration circuits using hot gas, off time or electric defrost
UNIVERSIAL INPUTS (UI)	None
DIGITAL INPUTS (DI)	None
DIGITAL OUTPUT (DO)	10 Form C Relay Outputs: SPDT, 2A, 250Vac. Protected by on-board fuses
ANALOG OUTPUT (AO)	None
DIMENSIONS	12.5" X 4.0" X 1.25" (318mm x 102mm x32mm)
MOUNTING	Plastic SnapTrck or SB Metal Enclosure
POWER REQUIREMENT	24Vac Center-tap 3.3VA
ENVIRONMENTAL	Operating and Storage: -40 to 75°C (-40 to 168°F), 5 to 95% RH, non-condensing
INSTALLATION TYPE	PART# 950634B: WITHOUT ENCLOSURE PART# 961634B: WITH ENCLOSURE PART# 962634B: ON SNAPTRACK

	08
	07
	06
	05
	04
--	03
--	02
--	01
--	00
DATE	DESCRIPTION REV.

SYSTEM :

REFRIGERATION

AUTOMATION / CONTROL :



2584 boul. La Conquisier
Laval, Quebec
Canada, H7S 2K6
Tel: (450) 688-3033
Fax: (450) 688-2695
e-mail : mt@microthermo.com

TITLE:

MT-CKT CIRCUIT CONTROLLER

PART# 9XX634B

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO. :
G.O.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO. :	FILE NAME :
N.T.S	08-24-2004	C-005	MT-CKT