





- NOTES:
- 1. SUPPLY AND OUTPUT SHARE COMMON GROUND.
 - 2. LOAD MUST BE EQUAL OR GREATER THAN 3000 Ω
 - 3. OUTPUT CAN BE SHORTED TO GROUND.
 - 4. DO NOT SHORT TO THE POSITIVE SUPPLY VOLTAGE.
 - 4. MOUNTING DIMENSIONS FOR REFERENCE ONLY

LEADWIRE COLOR CODE:
RED-SUPPLY VOLTAGE(+)
BLACK-GROUND(-)
GREEN OR WHITE-OUTPUT

SPECIFICATIONS

PART#: 9520001 (0-100psi)
9520002 (0-500psi)
9520004 (0-200psi)

SUPPLY VOLTAGE: 5VDC

SUPPLY CURRENT: 10mA MAX

OUTPUT SOURCE CURRENT: 0.5mA MAX

TEMPERATURE:(OPERATING AND STORAGE): -55 TO 125 °C
(-67 TO 257°F)

	08
	07
	06
	05
	04
---	03
---	02
---	01
---	00
DATE	DESCRIPTION
	REV.

SYSTEM :
REFRIGERATION

AUTOMATION / CONTROL :

MICRO THERMO

TECHNOLOGIES

2584 boul. Le Corbusier
Laval, Quebec
Canada, H7S 2K8
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail : mt@microthermo.com

TITLE:

PRESSURE TRANSDUCER

PART# 952000X

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO :
G.Q.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO :	FILE NAME:
N.T.S	08-26-2004	S-003	PROBE952000X