Fulflo® MegaBond Plus™ Cartridges

Depth Cartridge for High Dirt-Holding Capacity and Absolute-Rated Filtration Efficiency

Parker's Fulflo® MegaBond Plus™ (MBP) are absolute rated depth cartridges. Using a new innovative manufacturing process, the MBP has higher dirt-holding capacities offering long service life without contaminant migration. The MBP has a fixed core inner structure of thermally bonded continuous microfine polypropylene fibers. The modified outer layer fixed pore structure maximizes the graded density surface area to enhance dirt-holding capacity.

Available in absolute (B = 5000) ratings of 1, 3, 5, 10, 15, 20, 30, 40, 70, 90 and 120 micron.



Benefits

 Microfine, thermally bonded fiber construction provides superior filtration & often eliminates the need for circulation to achieve product clarity

Contact Information

Parker-Hannifin Corporation domnick hunter Process Filtration - North America 2340 Eastman Avenue Oxnard, California, USA 93030

toll free +1 877 784 2234 phone +1 805 604 3400 fax +1 805 604 3401 dhpsales.na@parker.com

www.parker.com/processfiltration



- Non-fiber-releasing, continuous fiber matrix prevents media migration and ensures consistent production yields and overall quality filtration performance
- No surfactants or binders are present to interrupt product quality or cause foaming
- Double open-end cartridges have polyolefin gaskets thermally bonded to both ends eliminating fluid bypass between the cartridge and the vessel seal
- Superior inter-layer bonding eliminates contaminant unloading and channeling
- Unique outer graded density structure increases dirt holding capacity
- Polypropylene fiber provides broad chemical compatibility for a variety of applications

- All materials of construction are FDA listed as acceptable for potable and edible liquid contact according to CFR Title 21
- Pore size differentiation is achieved using fibers of differing diameters and maintaining uniform density throughout the cartridge
- Pore sizes do not change as DP increases during service, providing consistent particle retention

Applications

- Photographics
- High Technology Coatings
- DI Water
- Plating Solutions
- Chemical Processing
- Membrane Prefiltration
- Food & Beverage

ENGINEERING YOUR SUCCESS.

Fulflo® MegaBond Plus™ Cartridges

Specifications

Materials of Construction:

Polypropylene:

Microfiber 100% melt blown construction

Center Support Core/End Caps:

Natural polypropylene

Thermally Bonded Gaskets:

Polyolefin closed cell foam (DOE only)

Maximum Recommended Operating Conditions:

Temperature:

@ 60psid (4.1bar): 80°F (27°C)
@ 35psid (2.4bar): 160°F (71°C)
@ 15psid (1.0bar): 200°F (93°C)

Flow Rate:

5gpm (18.9 lpm) per 10 in length

Recommended Maximum:

Change Out ΔP: 35psi (2.4bar) Operating Pressure @ Ambient Temperature: 60psid (4.1bar)

Dimensions:

1 in ID x $2-\frac{9}{16}$ in OD 10, 20, 30 and 40 in continuous nominal lengths

Absolute Filtration Ratings:

1μm, 3μm, 5μm, 10μm, 15μm, 20μm, 30μm, 40μm, 70μm, 90μm and 120μm

Beta Ratio (ß) =

Upstream Particle Count @ Specified Particle Size and Larger

Downstream Particle Count @ Specified Particle Size and Larger

Percent Removal Efficiency = $\left(\frac{\beta-1}{\alpha}\right)$ 100

Performance determined per ASTM F-795-88. Single-Pass Test using AC test dust in water at a flow rate of 3.5gpm per 10 in (13.2 lpm per 254 mm) cartridge.

MBP Flow Factors (psid/gpm @ 1 cks)

Rating (µm)	Flow Factor	
MBP1	2.17	
MBP3	1.60	
MBP5	0.90	
MBP10	0.32	
MBP15	0.16	
MBP20	0.12	
MBP30	0.10	
MBP40	0.05	
MBP70	<0.05	
MBP90	<0.04	
MBP120	<0.03	

MBP Length Factors

Length (in)	Length Factor	
9.75	1.0	
10.00	1.0	
19.50	2.0	
20.00	2.0	
29.25	3.0	
30.00	3.0	
39.00	4.0	
40.00	4.0	

Flow Rate and Pressure Drop Formulas

Flow Rate (gpm) = $\frac{\text{Clean } \Delta P \times \text{Length Factor}}{\text{Viscosity x Flow Factor}}$


Clean $\Delta P = Flow Rate x Viscosity x Flow Factor$ Length Factor

- 1. Clean ΔP is psi differential at start.
- 2. Viscosity is centistokes. Use Conversion Tables for other units.
- 3. Flow Factor is ΔP/GPM at 1cks for 10 in (or single).
- Length Factors convert flow or ΔP from 10 in (single length) to required cartridge length.

Liquid Particle Retention Ratings (µm) @ Removal Efficiency of:

Cartridge	ß=5000 Absolute	ß=1000 99.0%	ß=100 99%	ß=50 98%	ß=10 90%
MBP1	1	0.9	0.5	0.4	0.2
MBP3	3	2.8	1.9	1.7	0.8
MBP5	5	3.7	2.3	1.6	1.2
MBP10	10	9.1	8.0	7.8	6.7
MBP15	15	12.0	9.6	8.9	7.2
MBP20	20	18.3	13.0	12.5	8.7
MBP30	30	25.0	20.0	18.0	13.0
MBP40	40	35.0	28.0	25.0	18.0
MBP70	70	60.0	48.0	42.0	30.0
MBP90	90	80.0	72.0	63.0	48.0
MBP120	120	105.0	95.0	85.0	70.0

Ordering Information



	Support Construction					
s	CODE	MATERIAL				
\Box	N	Polypropylene				
	G	304 SS (Core Only)				
П						
_						

		End Cap Co	Seal Material				
	CODE	DESCRIPTION	CODE	DESCRIPTION	CODE	MATERIAL	
	None	Std. Double Open End (DOE) / Polyfoam	SSC	SS inserted 226 O-ring/Closed	None	Polyfoam (DOE only)	
_	AR	020/Flat (Gelman)	SSF	SS inserted 226 O-ring/Fin	Е	EPR	
	DO	DOE	STC	SS inserted 222 O-ring/Closed	N	Buna-N	
	DX	DOE with Polypro extender	STF	SS inserted 222 O-ring/Fin	S	Silicone	
	LL	120 O-ring both ends**	TC	222 O-ring/Flat		(O-ring only)	
	LR	120 O-ring/Recessed**	TF	222 O-ring/Fin		PFA Encapsulated	
	ОВ	Std. open end/Polypropylene spring closed end	TX	222 O-ring/Flex Fin	Т		
	PR	213 O-ring/Recessed**	XA	DOE w/Extended Core	V Viton®		
	SC	226 O-ring/Flat	ХВ	Ext. core open end/Polypropyl-		VILOIT	
	SF	226 O-ring/Fin		ene spring closed end			

**Available only in 9%" (9-4) and 19½" (19-4) lengths.

Specifications are subject to change without notification. For User Responsibility Statement, see www.parker.com/safety

120



© 2010 Parker-Hannifin Corporation domnick hunter Process Filtration - North America All Rights Reserved Viton is a registered trademark of E.I. DuPont de Nemours & Co., Inc.

DS_IP_MegaBond Plus Rev. A