


24/60/1Ø
WIRED FROM
TRANSFORMER



NOTE

2. TIGHTEN ALL ELECTRICAL CONNECTIONS BEFORE POWER IS APPLIED
3. USE #14 THIN MINIMUM FOR FIELD CONNECTIONS UNLESS OTHERWISE NOTED
4. ALL WIRING MUST BE DONE IN ACCORDANCE TO NEC AND
5. ALL OTHER LOCAL CODES.
6. ALL DRY CONTACTS RATED MINIMUM 250V, 5A

KEY:

DPST DOUBLE POLE SINGLE THROW SWITCH

		08
		07
		06
		05
		04
--	-----	03
--	-----	02
--	-----	01
----	-----	00
DATE	DESCRIPTION	REV.

SYSTEM

REFRIGERATION

AUTOMATION / CONTROL



MICRO THERMO

2584 boul. Le Corbusier
Laval, Quebec
Canada, H7S 2K8
Tel: (450) 668-3033
Fax: (450) 668-2695
e-mail: mt@micrOTHERM.com

TITLE: SCREW COMPRESSOR
(CEM) WIRING DIAGRAM
ECHELON MODULE

PART# 9XX632F

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO :
G.Q.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO :	FILE NAME:
N.T.S	08-24-2004	A-102	MTComp CEM