




- EACH CIRCUIT CONTROLLER CONTROLS A MAXIMUM OF FIVE REFRIGERATION CIRCUITS.
- 24VAC CENTER TAP TRANSFORMER REQUIRED (12VA PER CONTROLLER).
- RELAY OUTPUT RATING 2 Amps.
- SEE DRAWING C-005 FOR POWER REQUIREMENT.

LEGEND

- NET ————— NET ————— ECHOLON TYPE 2H16, STRANDED, 1929 UTP (UNSHIELDED TWISTED PAIR) BELDEN 8471 TYPE OR EQUIVALENT.
- PRE-WIRED CONNECTIONS
- FIELD INSTALLED WIRING
- FIELD INSTALLED BY ELECTRICIAN

REFRIGERATION

AUTOMATION / CONTROL :



2584 boul. Le Comusier
Laval, Quebec
Canada, H7S 2K6
Tel: (450) 688-3033
Fax: (450) 688-2695
e-mail : mt@mictthermo.com

TITLE: CIRCUIT CONTROLLER
CONNECTION DIAGRAM
24 VOLT POWER

PART# 9XX634B

DRAWN BY :	DESIGN BY :	APPROVED BY :	PROJECT NO. :
G.O.	L.M.	A.H.	STANDARD
SCALE :	DATE :	SHEET NO. :	FILE NAME :
N.T.S	08-23-2004	A-302	MT-CKT-CON-24V